



Data Sheet

HH-131-70×4-xx-PH3030



深圳市汉辉光电有限公司
shenzhen hanhui photoelectric co.,Ltd.

地址：深圳市宝安区石岩街道石龙仔社区恒昌荣高科技科技园3栋3楼
ADD: Area A No.3 Building 3th Floor,Hengchang Rong Industrial
park shiyan,shilong community,Bao'an District,shenzhen,china
TEL:86-755-29232420 FAX:86-755-83723765
<http://www.szhanhui.com> <http://linsen4880.1688.com>



Data Sheet

catalogue

General Information	P.1
Optical Specifications	P.2-5
Mechanical Specifications	P.6
Package Specifications	P.7

*Product Nomenclature

HH-131-70 × 4-xx - PH3030

H1

H2

H3

H4

H5

H6

H7

H1: The company's initials in Pinyin (Han Hui)

H2: Mold number

H3: Lens quantity

H4: The number of lamp beads inside each optical surface

H5: Lens angle/type (ex: 60、90、T2M、T3M)

H6: LED type (ex: CREE-CR、SAMSUNG-SS、PHILIPS-PH.....)

H7: LED size (ex:2835、3030、3535、.....)



HH-131-70×4-xx-PH3030

General Information

v1.0_20181009

◆ Features & Typical Applications

- Available with 5 beam angles
- High efficiency
- optimized Uniformity
- Lens without Holder
- Roadway Lighting
- Park Lighting
- Flood Lighting

◆ Material Information

Lens Material: PC 1225Z

Operating Temperature range $-40^{\circ}\text{C} \sim +110^{\circ}\text{C}$ (upper limit $+120^{\circ}\text{C}$).

Storage Temperature range $-40^{\circ}\text{C} \sim +110^{\circ}\text{C}$ (upper limit $+120^{\circ}\text{C}$).

*Average transmittance in visible spectrum $400\text{nm} \sim 700\text{nm} > 90\%$.

◆ Usage and Maintenance




1. If necessary, clean lenses with mild soap, water and soft cloth.
2. Never use any commercial cleaning solvents on lenses, like alcohol.
3. Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.






HH-131-70×4-xx-PH3030

Optical Specifications

v1.0_20181009

Part Number	FWHM	Field Angle*	cd/lm	IES File
HH-131-70×4-90-PH3030	93°	107°	0.52	Download
				
Beam Pattern	Candela Distribution	Illuminance Distribution		





Part Number	FWHM	Candela Distribution Type	IES File
HH-131-70×4-T5S- PH3030	120°	Type V Short	download
			



HH-131-70×4-xx-PH3030

Optical Specifications

v1.0_20181009




Part Number	FWHM	Candela Distribution Type	IES File
HH-131-70×4-T2M- PH3030	80×155	Type II Medium	Download
			
			
DIALux Simulation Result (two lanes、R3W3、ME4a)			
		Recommend configuration condition	
		Luminous Flux	17500lm
		Lamp Collocation	Unilateral
		Height	10m
		Distance	40m
		Roadwidth	7.5m
		Elevation	0°
		Overhang	1m
		Result	
		Lav	1.31
U ₀	0.47		
U _L	0.79		
TI(%)	12		
SR	0.69		
<p>Note: Lav-Average Luminance U₀-Brightness Uniformity U_L-Brightness longitudinal Uniformity TI-Threshold increment SR-Surround ratio</p>			



HH-131-70×4-xx-PH3030

Optical Specifications

v1.0_20181009





Part Number	FWHM	Candela Distribution Type	IES File
HH-131-70×4-T3M- PH3030	95×160	Type III Medium	Download
 <p>Polar Candela Distribution Plot</p>			
DIALux Simulation Result (three lanes、R3W3、ME4a)			
 <p>Note: Lav-Average Luminance U₀-Brightness Uniformity U_L-Brightness longitudinal Uniformity TI-Threshold increment SR-Surround ratio</p>		Recommend configuration condition	
		Luminous Flux	17500lm
		Lamp Collocation	Unilateral
		Height	10m
		Distance	40m
		Roadwidth	11.25m
		Elevation	0°
		Overhang	1m
		Result	
		Lav	0.91
U ₀	0.40		
U _L	0.76		
TI(%)	14		
SR	0.63		



HH-131-70×4-xx-PH3030

Optical Specifications

v1.0_20181009

Part Number	FWHM	Candela Distribution Type	IES File																												
HH-131-70×4-T4M- PH3030	95×155	Type IV Medium	Download																												
																															
																															
DIALux Simulation Result (four lanes、R3W3、ME4a)																															
 <p>Note: Lav-Average Luminance U₀-Brightness Uniformity U_L-Brightness longitudinal Uniformity TI-Threshold increment SR-Surround ratio</p>		<table border="1"> <thead> <tr> <th colspan="2">Recommend configuration condition</th> </tr> </thead> <tbody> <tr> <td>Luminous Flux</td> <td>17500lm</td> </tr> <tr> <td>Lamp Collocation</td> <td>Bilateral Symmetry</td> </tr> <tr> <td>Height</td> <td>10m</td> </tr> <tr> <td>Distance</td> <td>40m</td> </tr> <tr> <td>Roadwidth</td> <td>15m</td> </tr> <tr> <td>Elevation</td> <td>0°</td> </tr> <tr> <td>Overhang</td> <td>1m</td> </tr> <tr> <th colspan="2">Result</th> </tr> <tr> <td>Lav</td> <td>1.57</td> </tr> <tr> <td>U₀</td> <td>0.54</td> </tr> <tr> <td>U_L</td> <td>0.73</td> </tr> <tr> <td>TI(%)</td> <td>13</td> </tr> <tr> <td>SR</td> <td>0.65</td> </tr> </tbody> </table>		Recommend configuration condition		Luminous Flux	17500lm	Lamp Collocation	Bilateral Symmetry	Height	10m	Distance	40m	Roadwidth	15m	Elevation	0°	Overhang	1m	Result		Lav	1.57	U ₀	0.54	U _L	0.73	TI(%)	13	SR	0.65
		Recommend configuration condition																													
		Luminous Flux	17500lm																												
		Lamp Collocation	Bilateral Symmetry																												
		Height	10m																												
		Distance	40m																												
		Roadwidth	15m																												
		Elevation	0°																												
		Overhang	1m																												
		Result																													
Lav	1.57																														
U ₀	0.54																														
U _L	0.73																														
TI(%)	13																														
SR	0.65																														



HH-131-70×4-xx-PH3030

Mechanical Specification


v1.0_20181009

1. Fixing method


Note: (1) All dimensions are in mm.
(2) All measurements are ± 0.15 mm unless otherwise indicated.

- Glue Screw Tape Fixing-ring Frame

2. Lens dimension



3. Assembly instruction



4. View assembly lens with MCPCB




HH-131-70×4-xx-PH3030

Package Specifications

v1.0_20181009

Item	Quantity	Total	Size(L*W*H)	G.W
plastic box	-	15PCS	30*24*13cm	
outer box	4plastic box/outer box	50 PCS	63*26*29cm	



Note:

